



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR5351LA SGL Recp TR 20A/125V La

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | TR5351LA |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Single Receptacle, 20 A, 125 V, 2 Poles, 3 Wires, #14 to #10 Awg Compatible Wire Size, Back and Side Wired Connection, Wall Mount, 1.296 In Length, 1.190 In Width, 3.28 In Height, Nylon Material, Light Almond, Heavy Duty Corrosion Resistant, 0.1700 LB |
| Weight per unit | 0.1732 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|--|
| amperage rating | 20 |
| connection | Back and side wire |
| Dielectric Strength | Withstands 2000V minimum |
| indoor/outdoor | Indoor |
| media | Yes |
| Outlet Type | Tamper-Resistant |
| Poles | Double Pole |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wattage | Electrical power is expressed in Amps and Volts. |
| Wire Size | 14 - 10 |

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | SGL RECP TR 20A/125V LA |
| extra long description | P&S TR5351LA RECEP SGL TAMPER RESIS |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007241952 |
| Manufacturers Part Number | TR5351LA |
| UPC | 785007241952 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------|
| Category Description | Residential receptacles |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 100 |
| Weight Per each | 0.1732 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|--------------------------------|
| Application | Commercial |
| environmental conditions | Flammability: UL94 V2 |
| Mounting | WALL |
| standard | CULUS, UL498, CSA C22.2 No. 42 |
| Temperature Rating | -40° - 60° C |