



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR63HI TR Hosp Recp 20A 125V Iv

Pass & Seymour/LeGrand

| | |
|------------------|--|
| Catalog Number | TR63HI |
| Manufacturer | Pass & Seymour/LeGrand |
| Description | Tamper-Resistant Hospital Grade Receptacles, Back and Side Wire, 20A, 125V |
| Weight per unit | 0.2515 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|--|
| amperage rating | 20 |
| connection | Back and side wire |
| Dielectric Strength | Withstands 2000V minimum |
| indoor/outdoor | Indoor |
| Material | Nylon |
| media | Yes |
| Number of Wires | 3 |
| Outlet Type | Tamper-Resistant, Commercial, Indoor |
| Poles | Double Pole |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wattage | Electrical power is expressed in Amps and Volts. |
| Wire Size | 14 - 10 |

Material, Color, and Finish

| | |
|--------|-------|
| Color | Ivory |
| Finish | Matte |

Dimensions and Weight

| | |
|--------|-------|
| Height | 3.281 |
| Width | .900 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | TR HOSP RECP 20A 125V IV |
| extra long description | P&S TR63HI TAMPR RESISTNT HOSP RECP |
| Long Description | Tamper-Resistant Hospital Grade Receptacles, Back and Side Wire, 20A, 125V |
| Product Type | Tampr Resistnt Hosp Recp 20A 125V I |
| Special Features | Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects. Exclusive patented feature, circuit label on face allows permanent circuit identification. Extra heavy-duty brass, one-piece mounting strap with integral ground. One-piece, brass, triple-wipe power contacts for lasting retention. Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body. Impact-resistant nylon face and back body. Easily accessed break-off, line-contact conne |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007145250 |
| Manufacturers Part Number | TR63-HI |
| UPC | 785007145250 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | Commercial receptacles |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 100 |
| Weight Per each | 0.2515 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Commercial |
| environmental conditions | Flammability: UL94 V2 |
| Mounting | WALL |
| nema rating | 5-20R |
| standard | FEDSPEC, CULUS, UL498, CSA C22.2 No. 42 |
| Temperature Rating | -40° - 60° C |