



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TRVGF15WC 15A TR GFI WH *Eaton Wiring Devices*

| | |
|------------------|--|
| Catalog Number | TRVGF15WC |
| Manufacturer | Eaton Wiring Devices |
| Description | Gfci TR Deco Dup 15A 125V W/Mid WLPLT WH |
| Weight per unit | 0.4000 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|-----------------|---------------------------------------|
| amperage rating | 15 A |
| connection | 4714 Lm |
| Material | Nylon Top Housing, PVC Bottom Housing |
| Poles | 2 Pole/ 3 Wire |
| Voltage Rating | 125 A |

Dimensions and Weight

| | |
|-------|--------|
| Width | 1.3 in |
|-------|--------|

Descriptions

| | |
|------------------|---|
| Description | 15A TR GFI WH |
| Long Description | GFCI TR Deco Dup 15A 125V W/Mid Wlplt WH |
| Product Type | Gfci TR Deco Dup 15A 125V W/Mid WLPLT WH |
| Special Features | Specification Grade, Tamper Resistant, Wiring Type Back and Side Wire |

Manufacturer Information

| | |
|---------------------------|----------------------|
| Brand | Eaton Wiring Devices |
| GTIN | 00032664665776 |
| Manufacturers Part Number | TRVGF15W |
| sub brand | Arrow Hart |
| UPC | 032664665776 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------------|
| Category Description | Residential GFCI devices |
| Type | Duplex, GFCI, Straight Blade |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|-----|
| Carton | 10 |
| Package | 1 |
| Weight Per each | 0.4 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------------|---|
| Application | Specific Grade |
| Enclosure | Tamper Resistant NEC Requirements |
| standard | UL mA |