



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TY527MX 13.5" Uv Rated "Ty-Rap" Cable Tie

Abb Installation Products, Inc

Catalog Number	TY527MX
Manufacturer	Abb Installation Products, Inc
Description	High Performance Cable Tie, Black Color Nylon 6.6, Length Of 340.36MM (13.4 Inches) For Bundle Diameter Up to 102MM (4 Inches), Width Of 6.86MM (0.27 Inch), Tensile Strength Rating Of 534 Newtons (120 Pounds), Operating Temperature Of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F), 50 Pack
Weight per unit	0.0140 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Tensile Strength	120
------------------	-----

Dimensions and Weight

Length	13.5
Thickness	0.06
Width	0.27

Descriptions

Description	13.5" UV RATED "TY-RAP" CABLE TIE
extra long description	ABB TY527MX CBL TIE 120LB 13.4 UV B
Long Description	High Performance Cable Tie, Black Color Nylon 6.6, Length of 340.36mm (13.4 Inches) for Bundle Diameter up to 102mm (4 Inches), Width of 6.86mm (0.27 Inch), Tensile Strength Rating of 534 Newtons (120 Pounds), Operating Temperature of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F), 50 Pack
Product Type	CBL Tie 120LB 13.4 Uv Black
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time

Manufacturer Information

Brand	Ty-Rap
GTIN	00786210805122
Manufacturers Part Number	TY527MX
UPC	786210805122

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	HIGH PERFORMANCE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

minimum qty 50

Packaging

Carton 50

Package 500

Weight Per each 0.014

Uses, Certifications, and Standards

standard UL E49405