



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



U3278XLTG 200A 4T LVR Byp Nonlocking RNLGS Meter Socket

Milbank

Catalog Number	U3278XLTG
Manufacturer	Milbank
Description	Ringless Meter Socket, Ringless Meter Socket Accessory Type, Meter Socket Application, 200 A Current Rating, Type 3R Enclosure Type, Overhead/Underground Feed Type, Small Closing Plate Hub Type, Surface Mount, 4 - Jaws, 1 - Phases, 15.5 In Overall Height, 4.125 In Overall Length, 11 In Overall Width, 1 Ea Package Quantity, UI Listed, 600 V Voltage Rating, 13 LB Weight, #6 Awg - 350 Kcmil Wire Size
Weight per unit	13.0 (lbs/each)
Product Category	Residential Single Meter Socke

Features

amperage rating	200 Continuous Ampere
Bypass Type	Lever Bypass
Cable Entry	Overhead or Underground
cutout size	No Main Breaker
insulation	Glass Polyester
Phase	1 Phase

Dimensions and Weight

Size	4.125L x 11W x 15.5H
------	----------------------

Descriptions

Also Known As...	Meter Box Meter Socket
Description	200A 4T LVR BYPS NONLOCKING RNLGS METER SOCKET
extra long description	MILB U3278-XL-TG 200A 4T RL LVR OU

Manufacturer Information

Brand	MILBANK
GTIN	00784572323667
Manufacturers Part Number	U3278-XL-TG
UPC	784572323667

Taxonomies, Classifications, and Categories

Category Description	Meter Sockets
Type	Ringless Meter Socket

Packaging

Carton	2
Package	1
Weight Per each	13



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Enclosure	G90 Galvanized Steel with Powder Coat Finish
Frequency Rating	60 Hertz
Mounting	Surface Mount
standard	UL Listed; Type 3R