




MILBANK
ENERGY AT WORK

U3548-X



Catalog Number	U3548-X	Jaw Quantity	4 Terminal
Marketing Product Description	4 Terminal Ring Type Large Closing Plate Link Bypass	Bypass Type	Link Bypass
UPC	784572138490	Number of Meter Positions	1 Position
Length (IN)	6	Equipment Ground	Bonded Neutral
Width (IN)	14	Hub Opening	Large Closing Plate
Height (IN)	33	Line Side Wire Range	4 AWG - 600 kcmil or Two 1/0 AWG - 250 kcmil
Brand Name	Milbank	Load Side Wire Range	4 AWG - 600 kcmil or Two 1/0 AWG - 250 kcmil
Type	Ring Type Meter Socket	Number Of Receptacles	0
Application	Meter Socket		
Standard	UL Listed;Type 3R		
Voltage Rating	600 Volts Alternating Current		
Amperage Rating	320 Continuous Ampere		
Phase	1 Phase		
Frequency Rating	60 Hertz		
Size	6L x 14W x 33H		
Number Of Cutouts	0		
Cutout Size	No Main Breaker		
Cable Entry	Overhead or Underground		
Terminal	Single Mechanical		
Insulation	Glass Polyester		
Mounting	Surface Mount		
Enclosure	G90 Galvanized Steel with Powder Coat Finish		

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.