



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## U4908011GR 100A 1PH UG MTR SCKT W/ 2 Gfci Receptacles

Milbank

Catalog Number	U4908011GR
Manufacturer	Milbank
Description	4 Term RNLGS Plain Top 520GR 520GR Surf MNT
Weight per unit	25.0 (lbs/each)
Product Category	Metered Power Outlet Panels

### Features

amperage rating	125 Continuous Ampere
Bypass Type	No Bypass
Cable Entry	Underground
cutout size	Two Single Pole 20 Ampere Breakers
insulation	Glass Polyester
Phase	1 Phase
Voltage Rating	Up to 240 Volts Alternating Current

### Dimensions and Weight

Size	5.188L x 9W x 25.938H
------	-----------------------

### Descriptions

Also Known As...	Meter Box Meter Socket
Description	100A 1PH UG MTR SCKT W/ 2 GFCI RECEPTACLES
extra long description	MILB U4908-O-11GR 100A RL MTR P/O 2
Long Description	4 TERM RNLGS PLAIN TOP 520GR 520GR SURF MNT
Product Type	100A RL MTR P/O 27195
Special Features	Two Single Pole 20 Ampere Breakers

### Manufacturer Information

Brand	MILBANK
GTIN	00784572271951
Manufacturers Part Number	U4908-O-11GR
UPC	784572271951

### Taxonomies, Classifications, and Categories

Category Description	Meter Sockets
Type	Ringless Meter Socket

### Packaging

Carton	1
Weight Per each	25



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Temporary Power
Enclosure	G90 Galvanized Steel with Powder Coat Finish
Frequency Rating	60 Hertz
Mounting	Surface Mount
standard	UL Listed; Type 3R