



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



U5750RXL200BL 200A 3PH 7T Oh/Ug LVR Bypss MTR SCKT W/ Wireway Milbank

Catalog Number	U5750RXL200BL
Manufacturer	Milbank
Description	7 Term RINGLES LRG Hub Open Adapt to SML CLS PLT LVR Bypss 1-200 Amp MN BRKR 9-16- In BRL LCK With BRKT Prov
Weight per unit	53.0 (lbs/each)
Product Category	Commercial Meter Mains

Features

amperage rating	200 Continuous Ampere
Bypass Type	Lever Bypass
Cable Entry	Overhead or Underground
cutout size	One 200 Ampere Main Breaker
insulation	Glass Polyester
Phase	3 Phase
Voltage Rating	Up to 240 Volts Alternating Current

Dimensions and Weight

Size	5.75L x 17.375W x 34H
------	-----------------------

Descriptions

Also Known As...	Meter Socket Meter Box
Description	200A 3PH 7T OH/UG LVR BYPASS MTR SCKT W/ WIREWAY
extra long description	MILB U5750-RXL-200-BL 200A 7T RL OU
Long Description	7 TERM RINGLES LRG HUB OPEN ADAPT TO SML CLS PLT LVR BYPASS 1-200 AMP MN BRKR 9-16- IN BRL LCK WITH BRKT PROV
Product Type	200A 7T RL Ou HD LVR Main 32493

Manufacturer Information

Brand	MILBANK
GTIN	00784572324930
Manufacturers Part Number	U5750-RXL-200-BL
UPC	784572324930

Taxonomies, Classifications, and Categories

Category Description	Meter Sockets
Type	Ringless Meter Socket

Packaging

Carton	1
Weight Per each	53



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Meter Socket With Main
Enclosure	G90 Galvanized Steel with Powder Coat Finish
Frequency Rating	60 Hertz
Mounting	Surface Mount
standard	UL Listed; Type 3R