



U5949-O-5T9-CDOT



Catalog Number	U5949-O-5T9-CDOT
Marketing Product Description	5 Terminal Ringless Plain Top Lever Bypass 1 Main Breaker Provision 5th Terminal 9 O'clock Position Single Pedestal Direct Bury Cold Sequence Fuse Pullout Colorado DOT
UPC	784572652927
Length (IN)	10.25
Width (IN)	9.875
Height (IN)	80
Brand Name	Milbank
Type	Ringless Meter Socket
Special Features	Colorado DOT
Application	Meter Socket With Main And Load Center
Standard	UL Listed;Type 3R
Voltage Rating	Up to 240 Volts Alternating Current
Amperage Rating	200 Continuous Ampere
Phase	1 Phase
Frequency Rating	60 Hertz
Size	10.25L x 9.875W x 80H
Number Of Cutouts	6
Cutout Size	Breaker Provision

Cable Entry	Underground
Terminal	Single Mechanical
Insulation	Glass Polyester
Mounting	Pedestal
Enclosure	G90 Galvanized Steel with Powder Coat Finish
Jaw Quantity	5 Terminal
Bypass Type	Lever Bypass
Number of Meter Positions	Single Power Head
Equipment Ground	4 Barrel Ground Lug
Hub Opening	Plain Top
Line Side Wire Range	6 AWG - 350 kcmil
Load Side Wire Range	1 AWG - 300 kcmil
Number Of Receptacles	0

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.



U5949-O-5T9-CDOT



Catalog Number	U5949-O-5T9-CDOT
Marketing Product Description	5 Terminal Ringless Plain Top Lever Bypass 1 Main Breaker Provision 5th Terminal 9 O'clock Position Single Pedestal Direct Bury Cold Sequence Fuse Pullout Colorado DOT
UPC	784572652927
Length (IN)	10.25
Width (IN)	9.875
Height (IN)	80
Brand Name	Milbank
Type	Ringless Meter Socket
Special Features	Colorado DOT
Application	Meter Socket With Main And Load Center
Standard	UL Listed;Type 3R
Voltage Rating	Up to 240 Volts Alternating Current
Amperage Rating	200 Continuous Ampere
Phase	1 Phase
Frequency Rating	60 Hertz
Size	10.25L x 9.875W x 80H
Number Of Cutouts	6
Cutout Size	Breaker Provision

Cable Entry	Underground
Terminal	Single Mechanical
Insulation	Glass Polyester
Mounting	Pedestal
Enclosure	G90 Galvanized Steel with Powder Coat Finish
Jaw Quantity	5 Terminal
Bypass Type	Lever Bypass
Number of Meter Positions	Single Power Head
Equipment Ground	4 Barrel Ground Lug
Hub Opening	Plain Top
Line Side Wire Range	6 AWG - 350 kcmil
Load Side Wire Range	1 AWG - 300 kcmil
Number Of Receptacles	0

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.