



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



U7262RLTG 150A 1PH Oh 4T Meter Socket

Milbank

| | |
|------------------|---|
| Catalog Number | U7262RLTG |
| Manufacturer | Milbank |
| Description | Meter Socket, 150 A, 15-1/2 In Overall Height, 8 In Overall Width, 4-1/8 In Overall Length, Surface Mount, 1 Phase, Small Opening Hub, 4 Jaws, 600 V Ac, #6 Awg to 350 Kcmil Wire Size, Overhead/Underground Feed, 10.25 LB |
| Weight per unit | 10.3 (lbs/each) |
| Product Category | Residential Single Meter Socke |

Features

| | |
|-----------------|-----------------------|
| amperage rating | 150 Continuous Ampere |
| Bypass Type | No Bypass |
| Cable Entry | Overhead |
| cutout size | No Main Breaker |
| insulation | Glass Polyester |
| Phase | 1 Phase |

Dimensions and Weight

| | |
|------|---------------------|
| Size | 4.125L x 8W x 15.5H |
|------|---------------------|

Descriptions

| | |
|------------------------|-------------------------------------|
| Also Known As... | Meter Box Meter Socket |
| Description | 150A 1PH OH 4T METER SOCKET |
| extra long description | MILB U7262-RL-TG 150A 4T RL OH 1404 |

Manufacturer Information

| | |
|-------|----------------|
| Brand | MILBANK |
| GTIN | 00784572140479 |
| UPC | 784572140479 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------|
| Category Description | Meter Sockets |
| Type | Ringless Meter Socket |

Packaging

| | |
|-----------------|-------|
| Carton | 4 |
| Package | 1 |
| Weight Per each | 10.25 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|------------------|--|
| Enclosure | G90 Galvanized Steel with Powder Coat Finish |
| Frequency Rating | 60 Hertz |
| Mounting | Surface Mount |
| standard | UL Listed; Type 3R |