



MILBANK
ENERGY AT WORK

U9701-RRL-BL



Catalog Number	U9701-RRL-BL	Mounting	Surface Mount
Marketing Product Description	7 Terminal Ringless Large Hub Open Adapt To Small Hub Open 9-16 In Barrel Lock With Bracket Provision Lever Bypass	Enclosure	G90 Galvanized Steel with Powder Coat Finish
UPC	784572269521	Jaw Quantity	7 Terminal
Length (IN)	4.844	Bypass Type	Lever Bypass
Width (IN)	13	Number of Meter Positions	1 Position
Height (IN)	19	Equipment Ground	Ground Lug
Brand Name	Milbank	Hub Opening	Large Hub Opening Adapted to Small Hub Opening
Type	Ringless Meter Socket	Line Side Wire Range	6 AWG - 350 kcmil
Application	Meter Socket	Load Side Wire Range	6 AWG - 350 kcmil
Standard	UL Listed;Type 3R	Barrel Lock Provision	9/16 Inch Knockout and Angle Bracket for Barrel Lock Provision
Voltage Rating	600 Volts Alternating Current	Number Of Receptacles	0
Amperage Rating	200 Continuous Ampere		
Phase	3 Phase		
Frequency Rating	60 Hertz		
Size	4.844L x 13W x 19H		
Number Of Cutouts	0		
Cutout Size	No Main Breaker		
Cable Entry	Overhead or Underground		
Terminal	Lay in		
Insulation	Glass Polyester		

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.