



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UAG2100 2" Ua Sealtite Conduit, Bonded UI 100' *Southwire Company*

Catalog Number	UAG2100
Manufacturer	Southwire Company
Description	UI Liquid-Tuff™ Liquidtight Conduit, Type LFMC, 6200 Series, Liquidtight Flexible Metal Conduit. Hot Dipped Galvanized Low Carbon Steel, Flame Retardant PVC Jacket. Color: Gray, 2 Inch Diameter, 100 Foot Reel
Weight per unit	1.5 (lbs/ft)
Product Category	Flexible Metallic Conduit

Features

Inside Diameter	2.020/2.045
Material	Steel
outside diameter	2.340/2.375

Material, Color, and Finish

Color	Gray
Finish	PVC
Jacket Material	PVC

Dimensions and Weight

Length	100
--------	-----

Descriptions

Description	2" UA SEALTITE CONDUIT, BONDED UL 100'
extra long description	AFC 6207-30-00 2" LT UL LT LFMC GR
Features	UL LIQUIDTUFF™ Liquidtight Flexible Steel Conduit designed for use as a raceway for power, control and communication cables in accordance with Article 350 of the National Electrical Code.
Long Description	UL LIQUID-TUFF™ Liquidtight Conduit, Type LFMC, 6200 Series, Liquidtight Flexible Metal Conduit. Hot Dipped Galvanized Low Carbon Steel, Flame Retardant PVC Jacket. Color: Gray, 2 inch Diameter, 100 Foot Reel
Product Type	2" LT UI LT LFMC Gray 100' RL
Short Description	2" LT UL LT LFMC GRAY 100' RL
Special Features	UL bonded strip 3/8in - 1.25in for grounding. UL Liquidtight all sizes. Sunlight resistant. Flame retardant PVD jacket. Hot dipped zinc galvanized steel low carbon steel core.

Manufacturer Information

Brand	Flexible Conduit
GTIN	00077680148087
Manufacturers Part Number	6207-30-00
UPC	077680148087



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	Liquidtight Flexible Metal Conduit

Trade Size

Trade Size	2
------------	---

Packaging

Carton	100
Weight	1.46
Weight Per foot	1.49

Uses, Certifications, and Standards

Application	For Service Entrance Wiring Upto 6 FT
Temperature Rating	176