



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## UAG341000 3/4" Ua Sealrite Conduit, Bonded UI 1000' *Southwire Company*

Catalog Number	UAG341000
Manufacturer	Southwire Company
Description	Flexible Conduit, 3/4 In Trade Size, 1.03 to 1.05 In Conduit Outer Diameter, 0.82 to 0.84 In Conduit Inner Diameter, 1000 FT Length, Jack: PVC Material, Galvanized, Gray, 4.25 In Bend Radius, -80 °F, 60 °F (Wet), 70 °F (Oil), -30 °F (Low Temperature) Operating Temperature, 176 °F, 140 °F (Wet), 158 °F (Oil), -22 °F (Low Temperature) Operating Temperature, 49 LB/100 FT
Weight per unit	0.3800 (lbs/each)
Product Category	Flexible Metallic Conduit

### Features

Inside Diameter	0.820/0.840
outside diameter	1.030/1.050

### Material, Color, and Finish

Jacket Material	PVC
-----------------	-----

### Descriptions

Description	3/4" UA SEALTITE CONDUIT, BONDED UL 1000'
extra long description	AFC 6203-60-00 3/4" UL LT LFMC GRA
Features	UL LIQUIDTUFF™ Liquidtight Flexible Steel Conduit designed for use as a raceway for power, control and communication cables in accordance with Article 350 of the National Electrical Code.

### Manufacturer Information

GTIN	00077680120090
UPC	077680120090

### Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	Liquidtight Flexible Metal Conduit

### Packaging

Carton	1000
Weight Per each	0.38

### Uses, Certifications, and Standards

Temperature Rating	176
--------------------	-----