

# Specifications



Photo is representative

## Eaton UAT2R2332UFLCH

Eaton meter socket, Multi position resi service, 200A, Over/under, Large hub cover plate hub mounted, #6-350 kcmil, 4-jaw, 1-phase, #8-250 kcmil, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

### Product specifications

<b>TYPE</b>	Multi position resi service
<b>AMPERAGE RATING</b>	200A
<b>FEED TYPE</b>	Top/b
<b>NUMBER OF JAWS</b>	Four-
<b>PHASE</b>	Single phase
<b>ENCLOSURE</b>	063 alumi

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UAT2R2332UFLCH
<b>UPC</b>	782116997817
<b>PRODUCT LENGTH/DEPTH</b>	5.38 in
<b>PRODUCT HEIGHT</b>	14.13 in
<b>PRODUCT WIDTH</b>	24.31 in
<b>PRODUCT WEIGHT</b>	29 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed

### UTILITY APPROVALS



FL : M  
(Duke  
Energ  
Floric  
Powe  
Tamp  
Electr  
Gulf  
Powe  
Oklah  
Gas a  
Electr  
IN : M  
(Duke  
Energ  
Floric  
Powe  
Tamp  
Electr  
Gulf  
Powe  
Oklah  
Gas a  
Electr  
KY :  
(Duke  
Energ  
Floric  
Powe  
Tamp  
Electr  
Gulf  
Powe  
Oklah  
Gas a  
Electr  
NC :  
(Duke  
Energ  
Floric  
Powe  
Tamp  
Electr  
Gulf  
Powe  
Oklah  
Gas a  
Electr  
OH :  
(Duke