



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UNY27 3/4 NPT Male Uny Short Union

Crouse-Hinds

Catalog Number	UNY27
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Uny Expansion Union, Rigid/Imc, Male, Steel, 3/4", Short
Weight per unit	0.6300 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Male Threaded, Male Threaded
dimensions	2.1300 IN X 1.4400 IN X 1.4400 IN

Descriptions

Description	3/4 NPT MALE UNY SHORT UNION
extra long description	CRS-H UNY27 3/4 NPT MALE UNY SHORT
Features	Crouse-Hinds series explosionproof unions are installed in rigid/IMC conduit systems to connect conduit to conduit, a conduit fitting, junction box or device enclosure. Expansion unions are also available, which allow for expansion and contraction of conduit and compensate for conduit cut too short. Available in a variety of materials, including stainless steel, to suit customer preferences. Explosionproof elbows allow for a 90° change in direction to the conduit run, or when terminating at a box or fit
Long Description	Eaton Crouse-Hinds series UNY expansion union, Rigid/IMC, Male, Steel, 3/4", Short
Product Type	3/4 NPT Male Uny Short Union
Special Features	1-7/16 In Diameter X 3-3/8 In Length

Manufacturer Information

Brand	Eaton
GTIN	00782274129051
Manufacturers Part Number	UNY27
UPC	782274129051

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION FITTINGS
Type	Expansion union

Packaging

Carton	1
Weight Per each	0.63



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Class I Div 1 2 Group C D, Class II Div 1 Group E F G, Class II Div 2 Group F G, Class III
standard	UL 886, CSA C22.2