



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## URD4040204PCS 4/0-4/0-2/0-4 Urd Mobile Home Feeder Alu PCS

*King Wire Inc.*

Catalog Number	URD4040204PCS
Manufacturer	King Wire Inc.
Description	Type MC Cable, Flame Retardant;Moisture Resistant;Sunlight Resistant Additional Information, Mobile Home Application, Aluminum Alloy Conductor Material, 4/0-4/0-2/0-4 Awg Conductor Size, 200 A Current Rating, Polyethylene (XLpe) Insulation Material, 80 Mil Insulation Thickness, Made In Usa, +90 °C Maximum Operating Temperature, 1.380 In Outside Diameter, Reel Package Type, Strand Solid/Strand, Directive 2002/95/Ec;Federal Specification A-A-59544;Nec Nfpa 70, 2011 Edition;Rohs Compliant;UI 44;UI 84 Standard
Weight per unit	0.8080 (lbs/ft)
Product Category	Direct Burial Wire

### Descriptions

Description	4/0-4/0-2/0-4 URD MOBILE HOME FEEDER ALU PCS
-------------	----------------------------------------------

### Manufacturer Information

Brand	Aluminum
-------	----------

### Taxonomies, Classifications, and Categories

Category Description	Direct Burial Wire
----------------------	--------------------

### Packaging

Carton	1
Weight Per foot	0.808