

Specifications



Eaton URTRS101BE

Eaton meter socket, 3 5/16 in hub opening, 125A, Overhead, Hub opening, #8-2/0 kcmil, Four-jaw, Single-phase, #8-2/0 kcmil, Sockets:1, Three-wire, Ring, 600V

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	URTRS101BE
UPC	786685217826
PRODUCT LENGTH/DEPTH	3.63 in
PRODUCT HEIGHT	11 in
PRODUCT WIDTH	8.25 in
PRODUCT WEIGHT	7 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed



Product specifications

TYPE	3 5/16 in hub opening
AMPERAGE RATING	125A
FEED TYPE	Overhead
NUMBER OF JAWS	Four-jaw

Resources

CATALOGS	Residential and Light Commercial Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - URTRS101BE

PHASE	Single-phase
UTILITY APPROVALS	TN : Knoxville Utility Board (KUB)
LINE	#8-2/0 kcmil
LOAD	#8-2/0 kcmil
NUMBER OF WIRES	Three-wire
HUB TYPE	Hub opening
SECURITY	Ring
VOLTAGE RATING	600 V
NUMBER OF SOCKETS	1

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.



Specifications



Eaton URTRS101BE

Eaton meter socket, 3 5/16 in hub opening, 125A, Overhead, Hub opening, #8-2/0 kcmil, Four-jaw, Single-phase, #8-2/0 kcmil, Sockets:1, Three-wire, Ring, 600V

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	URTRS101BE
UPC	786685217826
PRODUCT LENGTH/DEPTH	3.63 in
PRODUCT HEIGHT	11 in
PRODUCT WIDTH	8.25 in
PRODUCT WEIGHT	7 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed



Product specifications

TYPE	3 5/16 in hub opening
AMPERAGE RATING	125A
FEED TYPE	Overhead
NUMBER OF JAWS	Four-jaw

Resources

CATALOGS	Residential and Light Commercial Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - URTRS101BE

PHASE	Single-phase
UTILITY APPROVALS	TN : Knoxville Utility Board (KUB)
LINE	#8-2/0 kcmil
LOAD	#8-2/0 kcmil
NUMBER OF WIRES	Three-wire
HUB TYPE	Hub opening
SECURITY	Ring
VOLTAGE RATING	600 V
NUMBER OF SOCKETS	1

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

