

Specifications



Eaton UTH7330UCH

Eaton meter socket, 1-pos commercial or resi service, 320A, Over/under, 5x5 inch hub cover plate, 3/8 inch stud, 7-jaw, three-phase, 3/8 inch stud, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 4-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UTH7330UCH
UPC	782116016686
PRODUCT LENGTH/DEPTH	6.5 in
PRODUCT HEIGHT	39.88 in
PRODUCT WIDTH	20 in
PRODUCT WEIGHT	60 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

TYPE	Single-position commercial or residential service
AMPERAGE RATING	320A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Seven-jaw
PHASE	Three-phase
UTILITY APPROVALS	ME : Central Maine Power NM : El Paso Electric TX : El Paso Electric AR : Entergy LA : Entergy MS : Entergy TX : Entergy KY : Louisville Gas & Electric/Kentucky Utilities TN : Middle Tennessee EMC
LINE	3/8 in stud
LOAD	3/8 in stud
NUMBER OF WIRES	Four-wire
HUB TYPE	5 x 5 hub cover plate
SECURITY	Ringless
VOLTAGE RATING	600 V
BYPASS	Lever
NUMBER OF SOCKETS	1

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UTH7330UCH
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Eaton UTH7330UCH

Eaton meter socket, 1-pos commercial or resi service, 320A, Over/under, 5x5 inch hub cover plate, 3/8 inch stud, 7-jaw, three-phase, 3/8 inch stud, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 4-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UTH7330UCH
UPC	782116016686
PRODUCT LENGTH/DEPTH	6.5 in
PRODUCT HEIGHT	39.88 in
PRODUCT WIDTH	20 in
PRODUCT WEIGHT	60 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

TYPE	Single-position commercial or residential service
AMPERAGE RATING	320A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Seven-jaw
PHASE	Three-phase
UTILITY APPROVALS	ME : Central Maine Power NM : El Paso Electric TX : El Paso Electric AR : Entergy LA : Entergy MS : Entergy TX : Entergy KY : Louisville Gas & Electric/Kentucky Utilities TN : Middle Tennessee EMC
LINE	3/8 in stud
LOAD	3/8 in stud
NUMBER OF WIRES	Four-wire
HUB TYPE	5 x 5 hub cover plate
SECURITY	Ringless
VOLTAGE RATING	600 V
BYPASS	Lever
NUMBER OF SOCKETS	1

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UTH7330UCH
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

