

CONNECTORS

Mechanical Connectors

Aluminum Service Wedge Clamps

W Series



SPECIFICATIONS

- UL486A Listed for Wire Connector.
- Temperature Rating: 90 °C
- Voltage: 600V max.

FEATURES

- For dead-ending self-supporting drop wire.
- Saves conductor — drop wire may be cut to exact length.
- Can be attached to bare neutral in any point in the span.
- Adjustment in drop wire sag are easily made.
- Grips ACSR, AAAC or aluminum conductor.
- Catalog number with "FC" suffix have a Flexible bail.



CAT. NO.	FIG. NO.	WIRE RANGE			LENGTH (L)	WIDTH (W)	STD. CTN. QTY.
		ACSR	ALUMINUM	AAAC			
W62-1	1	2-6	1 STR-6 SOL	2-6	12.000	2.375	12
W62-1FC	2	2-6	1 STR-6 SOL	2-6	17.500	FLEX	12
W20-1	1	1/0-4	2/0 STR-2 SOL	1/0-4	12.500	2.375	8
W20-1FC	2	1/0-4	2/0 STR-2 SOL	1/0-4	18.500	FLEX	8
W40-1	1	4/0-2/0	4/0 STR-2/0 SOL	4/0-2/0	12.750	2.375	6
W40-1FC	2	4/0-2/0	4/0 STR-2/0 SOL	4/0-2/0	18.500	FLEX	6

CONNECTORS

Mechanical Connectors

Aluminum Service Wedge Clamps W Series




SPECIFICATIONS

- UL486A Listed for Wire Connector.
- Temperature Rating: 90 °C
- Voltage: 600V max.

FEATURES

- For dead-ending self-supporting drop wire.
- Saves conductor — drop wire may be cut to exact length.
- Can be attached to bare neutral in any point in the span.
- Adjustment in drop wire sag are easily made.
- Grips ACSR, AAAC or aluminum conductor.
- Catalog number with “FC” suffix have a Flexible bail.



CAT. NO.	FIG. NO.	WIRE RANGE			LENGTH (L)	WIDTH (W)	STD. CTN. QTY.
		ACSR	ALUMINUM	AAAC			
W62-1	1	2-6	1 STR-6 SOL	2-6	12.000	2.375	12
W62-1FC	2	2-6	1 STR-6 SOL	2-6	17.500	FLEX	12
W20-1	1	1/0-4	2/0 STR-2 SOL	1/0-4	12.500	2.375	8
W20-1FC	2	1/0-4	2/0 STR-2 SOL	1/0-4	18.500	FLEX	8
W40-1	1	4/0-2/0	4/0 STR-2/0 SOL	4/0-2/0	12.750	2.375	6
W40-1FC	2	4/0-2/0	4/0 STR-2/0 SOL	4/0-2/0	18.500	FLEX	6