



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WACDC2SPL Accessory Dimmer, (W, La, Iv)

Eaton Wiring Devices

Catalog Number	WACDC2SPL
Manufacturer	Eaton Wiring Devices
Description	Eaton Wi-Fi Smart Dimmer, Flush, 120V, Back and Side Wire, White, Ivory, and Light Almond, Single-Pole, Three-Way, 32°F to 104°F (0°C to 40°C), Single-Phase, Multi-Location, PC/PBT, WFD30, Wifi
Weight per unit	0.3700 (lbs/each)
Product Category	Wiring Devices

Features

dimensions	2.3600 IN X 3.7700 IN X 7.4300 IN
Phase	Single-phase
Voltage Rating	120 V

Descriptions

Description	ACCESSORY DIMMER, (W, LA, IV)
extra long description	EWD WACD-C2-SP-L Accessory Dimmer,
Features	Wi-fi smart switches, receptacles, and dimmers from Eaton set up quickly and easily with Amazon's Alexa app—no other hubs or controllers are necessary. Plus Frustration Free Setup starts the connection automatically. Schedule lights to go on and off—and even dim—to fit your daily routine. Save energy and feel more comfortable and secure. You can even add voice-control using an Amazon Echo device.
Long Description	Eaton Wi-Fi smart dimmer, Flush, 120V, Back and side wire, White, Ivory, and Light Almond, Single-pole, Three-way, 32°F to 104°F (0°C to 40°C), Single-phase, Multi-location, PC/PBT, WFD30, WiFi
Product Type	Accessory Dimmer, (W, La, Iv)

Manufacturer Information

Brand	Eaton
GTIN	00786689366698
Manufacturers Part Number	WACD-C2-SP-L
UPC	786689366698

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Accessory



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	32
Weight Per each	0.37

Uses, Certifications, and Standards

Application	Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other
Operating Temperature standard	32 to 104 °F (0 to 40 °C) cULus Listed