



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **WAGS4010 #14-4/0 Wrap-Around Gel Splice Kit, 10" Length**

*Nsi Industries*

|                  |   |
|------------------|---|
| Catalog Number   | WAGS4010  |
| Manufacturer     | Nsi Industries  |
| Description      | Easy-Splice Wrap Around Gel Splice Kit - #4/0 to 14 Awg - 10 Inch Easy-Splice Wrap-Around Gel Splice Closure Sleeves Quickly Insulate and Seal Buried Electrical Connections Rated Up to 1,000 Volts. Engineered to Handle Direct Burial and Manhole Applications, These Splice Enclosure Sleeves Are Equally Well Suited For Insulation and Jacket Repair. Simply Wrap and Snap The Sleeve On Any Cable In The Use Range. The Sealant Gel In The Sleeve Seals On Contact. The Splice Closure Sleeve Can Be Applied On All Comm |
| Weight per unit  | 0.4600 (lbs/each)   |
| Product Category | Splicing & Terminating Kits   |

### **Features**

|                |            |
|----------------|------------|
| Cable Size     | 4/0-14 AWG |
| Cable Type     | Class A-B  |
| Voltage Rating | 1000 V     |
| Warranty       | 1 YEAR     |

### **Material, Color, and Finish**

|       |       |
|-------|-------|
| Color | Black |
|-------|-------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | #14-4/0 WRAP-AROUND GEL SPLICE KIT, 10" LENGTH  |
| extra long description | NSI WAGS-4/0-10 Easy-Splice Wrap-Ar   |
| Features               | Easy-Splice Wrap Around Gel Splice Kit - #4/0 to 14 AWG - 10 Inch Easy-Splice wrap-around gel splice closure sleeves quickly insulate and seal buried electrical connections rated up to 1,000 volts. Engineered to handle direct burial and manhole applications, these splice enclosure sleeves are equally well suited for insulation and jacket repair. Simply wrap and snap the sleeve on any cable in the use range. The sealant gel in the sleeve seals on contact. The splice closure sleeve can be applied on all comm |
| Long Description       | Easy-Splice Wrap Around Gel Splice Kit - #4/0 to 14 AWG - 10 Inch Easy-Splice wrap-around gel splice closure sleeves quickly insulate and seal buried electrical connections rated up to 1,000 volts. Engineered to handle direct burial and manhole applications, these splice enclosure sleeves are equally well suited for insulation and jacket repair. Simply wrap and snap the sleeve on any cable in the use range. The sealant gel in the sleeve seals on contact. The splice closure sleeve can be applied on all comm |
| Product Type           | Easy-Splice Wrap-Around 4/0 10"   |
| Special Features       | Wrap Around Gel Splice For Fast Installation - 10 Sleeve Length   |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSi            |
| GTIN                      | 00662381015709 |
| Manufacturers Part Number | WAGS-4/0-10    |
| UPC                       | 662381015709   |

## Taxonomies, Classifications, and Categories

|                      |                             |
|----------------------|-----------------------------|
| Category Description | SPLICE KITS                 |
| Type                 | Wrap Around Gel Splice Kits |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 3    |
| Weight Per each | 0.46 |

## Uses, Certifications, and Standards

|                                |   |
|--------------------------------|---|
| Application                    | Splicing Wire                               |
| Operating Temperature standard | -40 C To 90 C<br>ANSI C119.1-1986 Qualified |