



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WCBSJ Wire Guards Blue Esy Twist 300 PC Jar

Nsi Industries

Catalog Number	WCBSJ
Manufacturer	Nsi Industries
Description	Twist-On Wire Connector, (2) #22 Awg Conductor Size, (3) #16 Awg Conductor Size, Insulated, Thermoplastic Insulation Material, Copper Conductor Material, Blue Insulation Color, +221 °F Operating Temperature, 0.161 In Overall Width, 0.697 In Overall Height, 300 V, 0.55 LB
Weight per unit	0.5500 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Thermoplastic
Voltage Rating	300 V
Warranty	1 YEAR
Wire Type	COPPER

Material, Color, and Finish

Color	Blue
Finish	Thermoplastic

Dimensions and Weight

Depth	.161
Height	.697

Descriptions

Description	WIRE GUARDS BLUE ESY TWIST 300 PC JAR
extra long description	NSI WC-B-SJ Easy-Twist Blue - Std J

Manufacturer Information

GTIN	00662381142399
UPC	662381142399

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Standard Wire Connectors

Packaging

Carton	1
Weight Per jar	0.55

Uses, Certifications, and Standards

Application	Splicing Wire
environmental conditions	105 C
standard	UL 486C