



121.5 mm


Figure/Figura 1. (A) Single gang/Sola cuadrilla




Figure/Figura 1. (B)



Figure/Figura 2



Figure/Figura 3



www.passandseymour.com  
1-800-223-4185

P/N 362733

362733 WIUCast Card.indd 1



Wet Locations

Pass &amp; Seymour

legrand®

Cat  
No:

WIUCAST1

Cast While-In-Use Cover

Vertical or Horizontal

Meets NEC 406.8(B) "Extra Duty"

Inserts for GFCI, Duplex, and  
Single Receptacles

Gray



1

PC



P.O. Box 4822, Syracuse, NY 13221-4822

Made in India

See instructions on reverse side.  
Ver instrucciones por la parte atrás.

▲ **WARNING:** Cancer and Reproductive Harm - www.P65Warnings.ca.gov▲ **ADVERTENCIA:** Cáncer y Daño Reproductivo - www.P65Warnings.ca.gov

6/1/11 10:31 AM

## INSTALLATION INSTRUCTIONS

This cover should be installed in areas subject to saturation from water or other liquids. (See description for "Wet Location" and "Damp Location" in the National Electrical Code). The single gang cover can be mounted horizontally or vertically as long as the hinge is in the top corner. See Figure 1 (A-B) for applicable mounting and attachment options.

**WARNING – Turn off all power to circuit before installing this device. Improper wiring of any electrical device can cause serious injury or death. These wiring devices should only be installed by an Electrician or other qualified person.**

**CAUTION – This cover should be installed in accordance with the National Electrical Code, and all applicable local codes and standards.**

## INSTALLATION INSTRUCTIONS

NOTE: The cover should be installed on a smooth, flat, non-porous surface. To install on an irregular surface, use a proper amount of caulking to ensure a watertight seal between the back of the cover and the mounting surface.

1. Disconnect power to circuit by removing fuse or turn breakers to OFF before installing.
2. Remove the existing receptacle cover, if any, and discard.
3. Back off the mounting screws that hold the GFCI or receptacle to the junction box but do not remove screws.
4. Insert mounting screws through the keyhole shaped mounting holes on assembly and slide the assembly to the left (see Figure 2). Center the device in the box. Tighten screws.
5. If mounting to an FS or outdoor junction box use the four screws provided to further secure the assembly to the box.
6. DO NOT OVER TIGHTEN SCREWS.
7. Choose appropriate insert and snap in by putting one long edge in place first and rotating the plate over the device. (If device is in the way, loosen screws and move left or right). Discard other Insert(s).
8. For best rain protection, be sure to route cords through the cord outlet and press the cover firmly until it snaps closed. Position cord gaskets (see Figure 3).

## INSTRUCCIONES DE INSTALACIÓN

La tapa debe ser instalada en áreas sujetas a saturación por agua u otros líquidos, (véase la descripción para "Localización Mojada" y "Localización Húmeda" en el Código Nacional Eléctrico). La sola tapa puede ser montada horizontalmente o verticalmente, mientras la bisagra está en la esquina de arriba. Véase la Figura 1 (A-B) para opciones aplicables de montaje y enganche.

**ADVERTENCIA – Apáguele la corriente al circuito antes cuadrilla de instalar este aparato. Alambrado impropio de cualquier aparato eléctrico puede causar serios daños o muerte. Estos aparatos eléctricos solamente deben ser instalados por un electricista u otra persona calificada.**

**CUIDADO – Esta tapa debe ser instalada de acuerdo con el Código Eléctrico Nacional y todas las códigos locales aplicables.**

## INSTRUCCIONES DE INSTALACIÓN

NOTA: La tapa debe ser instalada en una superficie lisa, plana y no porosa. Para instalar en una superficie irregular, utilice suficiente sellante para asegurar un sello a prueba de agua entre la parte de atrás y la superficie de montaje.

1. Desconéctele la corriente al circuito quitando el fusible o APAGANDO el disyuntor antes de instalar.
2. Quite la tapa del enchufe, si hay, y descarte.
3. Afloje los tornillos que aguantan el GFI o enchufe a la caja de pared, pero no quite los tornillos.
4. Introduzca los tornillos de montaje a través de los huecos de montaje tipo bocallave en el ensamblaje y deslice el ensamblaje hacia la izquierda (véase la Figura 2). Centre el aparato en la caja. Apriete los tornillos.
5. Si monta en una caja de distribución de afuera o un FS, utilice los cuatro tornillos provistos para asegurar mejor el ensamblaje a la caja.
6. NO REQUINTE LOS TORNILLOS.
7. Elija el parte móvil apropiado y encájese a presión adentro poniendo un borde largo en el lugar primero y girando la placa sobre el dispositivo. (Si el dispositivo está de la manera, afloje los tornillos y mueva izquierdo o derecho). Deseche el otro parte móvil(s).
8. Para la mejor protección ante la lluvia asegúrese que ponga los cables a través de la salida del cable y apriete bien la tapa hasta que se tranque. Ponga las juntas del cable como se muestra en la Figura 3.

76 mm

76 mm