

Glare Free



WATTS: 86

WLD86LED

CCT: 4500K

CCT: 3000K

LUMENS: 9,173

LUMENS: 8,560

LPW: 107 CRI: 83

LPW: 98 CRI: 81

DIMMING: 10-100%

DIMMING: 10-100%

Design is Protected by U.S. Patent No. 9,482,395



Ordering Information


CATALOG #	DESCRIPTION	VOLTS	COLOR TEMP
WLD86LED	86W LED Wall Light	120-277	4500K
WLD86LED3K	86W LED Wall Light	120-277	3000K

Options

ADD SUFFIX #	DESCRIPTION
PC	120V Photocontrol
PM	208-277V Photocontrol
EB	Emergency Back-Up
4	480V Driver

Note: Atlas uses only premium LED compatible photocontrols

Recommended Mounting Height - 20-22 ft.



Mtg. Hgt.	FOOTCANDLES ON THE GROUND						Avg. FCs 450 SQ. FT.
	90°			45°			
	5'	10'	15'	5'	10'	15'	
20'	12.2	7.2	5.2	11.5	7.9	4.8	8.1
22'	10.4	6.8	4.6	9.6	7.2	4.6	7.2

Performance

- 95% Efficient Reflector Targets the Light
- Eliminates Glare & Offensive Light
- Less Wasted Light
- More Footcandles on the Ground
- Creates a Smooth & Uniform Light Pattern



Dimensions and Specifications

Overall Height: 9.01"

Depth: 9.78"

Overall Width: 18.2"

Weight: 15 lbs.



*The majority of Atlas Lighting Products are assembled in USA facilities by an American Workforce utilizing both Domestic and Foreign components

