Wall Light
27 Watt LED

Glare Free





Patent Pending

WATTS: 27 **WLSG27LED**

CCT: 4500K	**CCT: 3000K**
LUMENS: 3,017	**LUMENS: 2,749**
LPW: 113 CRI: 82	**LPW: 105 CRI: 81**
DIMMING: 10-100%	**DIMMING: 10-100%**

DLC QPL LISTED

MANUFACTURED* & TESTED IN USA

Ordering Information


CATALOG #	DESCRIPTION	VOLTS	COLOR TEMP
WLSG27LED	27W LED Wall Light	120-277	4500K
WLSG27LED3K	27W LED Wall Light	120-277	3000K

Options

ADD SUFFIX #	DESCRIPTION
PC	120V Photocontrol
PM	208-277V Photocontrol

Note: Atlas uses only premium LED compatible photocontrols

Recommended Mounting Height - 10-12 ft.



FOOTCANDLES ON THE GROUND							
Mtg. Hgt.	90°			45°			Avg. FCs 450 SQ. FT.
	5'	10'	15'	5'	10'	15'	
10'	7.2	3.3	1.8	6.8	4.4	2.3	**4.3**
12'	5.6	3.0	1.8	5.3	3.7	2.3	**3.6**

200,000+ HOURS

THERMAL STACKING

c UL us LISTED


5 YEAR WARRANTY

Performance

- **Eliminates Glare & Offensive Light**
- **Less Wasted Light**
- **More Footcandles on the Ground**
- **Creates a Smooth & Uniform Light Pattern**

Dimensions and Specifications

Overall Height: 8.5"
Overall Width: 8.75"
Depth: 9.05"
Weight: 6.6 lbs.



*The majority of Atlas Lighting Products are assembled in USA facilities by an American Workforce utilizing both Domestic and Foreign components

Wall Light
27 Watt LED

Glare Free





Patent Pending

WATTS: 27 **WLSG27LED**

CCT: 4500K	**CCT: 3000K**
LUMENS: 3,017	**LUMENS: 2,749**
LPW: 113 CRI: 82	**LPW: 105 CRI: 81**
DIMMING: 10-100%	**DIMMING: 10-100%**

DLC QPL LISTED

MANUFACTURED* & TESTED IN USA

Ordering Information


CATALOG #	DESCRIPTION	VOLTS	COLOR TEMP
WLSG27LED	27W LED Wall Light	120-277	4500K
WLSG27LED3K	27W LED Wall Light	120-277	3000K

Options

ADD SUFFIX #	DESCRIPTION
PC	120V Photocontrol
PM	208-277V Photocontrol

Note: Atlas uses only premium LED compatible photocontrols

Recommended Mounting Height - 10-12 ft.



FOOTCANDLES ON THE GROUND							
Mtg. Hgt.	90°			45°			Avg. FCs 450 SQ. FT.
	5'	10'	15'	5'	10'	15'	
10'	7.2	3.3	1.8	6.8	4.4	2.3	**4.3**
12'	5.6	3.0	1.8	5.3	3.7	2.3	**3.6**

200,000+ HOURS

THERMAL STACKING

c UL us LISTED


5 YEAR WARRANTY

Performance

- **Eliminates Glare & Offensive Light**
- **Less Wasted Light**
- **More Footcandles on the Ground**
- **Creates a Smooth & Uniform Light Pattern**

Dimensions and Specifications

Overall Height: 8.5"
Overall Width: 8.75"
Depth: 9.05"
Weight: 6.6 lbs.



*The majority of Atlas Lighting Products are assembled in USA facilities by an American Workforce utilizing both Domestic and Foreign components