



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WP3450LA Cat 5E RJ45 T568 A/B Conn La (M20)

Pass & Seymour/Legrand

|                  |                                                                                                                                                                                             |
|------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | WP3450LA                                                                                                                                                                                    |
| Manufacturer     | Pass & Seymour/Legrand                                                                                                                                                                      |
| Description      | Keystone Connector, Snap-In Connection, 5 Category Level, Light Almond, 1.28 In Length, 0.64 In Width, 0.87 In Height, +14 °F Operating Temperature, +140 °F Operating Temperature, 0.04 LB |
| Weight per unit  | 0.0391 (lbs/each)                                                                                                                                                                           |
| Product Category | Outlets, Jacks, & Plates                                                                                                                                                                    |

### Features

|                |                                                   |
|----------------|---------------------------------------------------|
| connection     | RJ45 Female                                       |
| Current Rating | 1.5 (@ 20 degrees C)                              |
| insulation     | Electrical Insulation Resistance: 500 (@ 100 VDC) |

### Material, Color, and Finish

|        |                                                           |
|--------|-----------------------------------------------------------|
| Finish | Molded plastic chemically etched with diamond core finish |
|--------|-----------------------------------------------------------|

### Dimensions and Weight

|      |                                           |
|------|-------------------------------------------|
| Size | 0.67 x 076 x 1.18 (17.02 x 19.30 x 29.97) |
|------|-------------------------------------------|

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | CAT 5E RJ45 T568 A/B CONN LA (M20)  |
| extra long description | OnQ WP3450LA CAT 5E RJ45 T568 A/B C |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Legrand On-Q   |
| GTIN                      | 00804428024866 |
| Manufacturers Part Number | WP3450LA       |
| UPC                       | 804428024866   |

### Taxonomies, Classifications, and Categories

|                      |                                        |
|----------------------|----------------------------------------|
| Category Description | Datacom Wiring Devices and Accessories |
| Type                 | RJ45 Female Cat 5e Keystone Insert     |

### Packaging

|                 |        |
|-----------------|--------|
| Carton          | 20     |
| Package         | 120    |
| Weight Per each | 0.0391 |

### Uses, Certifications, and Standards

|                          |                                                                  |
|--------------------------|------------------------------------------------------------------|
| Application              | Residential                                                      |
| environmental conditions | 0 to 93 (relative humidity, non-condensing)                      |
| Mounting                 | Keystone opening                                                 |
| standard                 | CSA, cULus, RoHS, ANSI/UL 1863, Flame-Retardant Plastic UL 94V-0 |
| Temperature Rating       | 14 to 140 F (-10 to 60 C)                                        |