



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10917 Mill Creek Rd
66219-0000, KS Lenexa
Phone: 913-563-7000
Fax: 913-563-7050



WT411 Wingtwist Wire Connector, WT41 Tan, 100/Box

Ideal

Catalog Number	WT411
Manufacturer	Ideal
Description	Buchanan, Wire Connector, Wingtwist, Conductor Range: 22 - 10 Awg, 2/20 Awg Min, 3/10 Solid Awg Max, Number Of Conductors: 1 to 6, Material: Flame-Retardant Polypropelene, Color: Tan, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Model Number: WT41
Weight per unit	0.5000 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Flame-retardant Polypropelene
Voltage Rating	600

Material, Color, and Finish

Color	Tan
-------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10917 Mill Creek Rd
66219-0000, KS Lenexa
Phone: 913-563-7000
Fax: 913-563-7050

Descriptions

Description	WINGTWIST WIRE CONNECTOR, WT41 TAN, 100/BOX
extra long description	IDEAL WT41-1 WINGTWIST WT41 TAN, 10
Features	With a full line for virtually every wire size and combination, the WingTwist Wire Connector offers a great combination of performance and value. The contoured wing design of the WingTwist provides maximum torque for a variety of electrical applications while the copolymer shell and live-action spring expand for smooth, progressive tightening providing dependable connections. With a tough, flame-retardant shell that withstands environmental extremes, and a long, deep skirt to provide maximum dielectric protection.
Long Description	Buchanan, Wire Connector, WingTwist, Conductor Range: 22 - 10 AWG, 2/20 AWG Min, 3/10 Solid AWG MAX, Number Of Conductors: 1 to 6, Material: Flame-retardant Polypropylene, Color: Tan, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: WT41
Product Type	Wingtwist WT41 Tan, 100 Box
Special Features	1,000V Maximum In Fixtures And Signs; Deep, Wide-Throated Skirt Protects Against Flash-Over And Turned-Back Strands For Maximum Dielectric Protection; Features: Five Color-Coded Models Cover Common Construction Wire Ranges; Fixed, Square-Wire Spring Threads Itself Creating Secure Pressure Grip; Green Model Designed For Ground Connections; Model Number: WT41; UL 486C Listed (WGR UL 467 Listed) And CSA C22.2 #188 Certified; Unique Contoured Wing Design Acts As Built-In Wrench Providing Maximum Torque With Minimum Effort

Manufacturer Information

Brand	Ideal
GTIN	00781789967660
Manufacturers Part Number	WT41-1
UPC	781789967660

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
----------------------	-----------

Availability

minimum qty	100
-------------	-----

Packaging

Carton	100
Package	1000
Weight Per each	0.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10917 Mill Creek Rd
66219-0000, KS Lenexa
Phone: 913-563-7000
Fax: 913-563-7050

Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA C22.2 #188, UL 486C Listed, RoHS