

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

21330 Inverness Forest Blvd 77073-0000, TX Houston Phone: 832-626-1994 Fax: 832-626-1995



WT41B Wingtwist Wire Connector, WT41 Tan, 500/Bag Ideal

Catalog Number	WT41B
Manufacturer	ldeal
Description	Buchanan, Wire Connector, Wingtwist, Conductor Range: 22 - 10 Awg, 2/20 Awg Min, 3/10 Solid Awg Max, Number Of Conductors: 1 to 6, Material: Flame-Retardant Polypropelene, Color: Tan, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Model Number: WT41
Weight per unit	0.0040 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts
Features	
Material	Flame-retardant Polypropelene
media	Yes
Voltage Rating	600
Material, Color, and Finish	
Color	Tan



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

21330 Inverness Forest Blvd 77073-0000, TX Houston Phone: 832-626-1994

Fax: 832-626-1995

. 1	2	$\alpha \mathbf{r}_{\mathbf{l}}$	m'	••	\sim	20
	es	1 - F I				1
_			•	LI	•	1.3

Description	WINGTWIST WIRE CONNECTOR, WT41 TAN, 500/BAG
extra long description	IDEAL WT41-B WINGTWIST WT41 TAN, 50
Features	With a full line for virtually every wire size and combination, the WingTwist Wire Connector offers a great combination of performance and value. The contoured wing design of the WingTwist provides maximum torque for a variety of electrical applications while the copolymer shell and live-action spring expand for smooth, progressive tightening providing dependable connections. With a tough, flame-retardant shell that withstands environmental extremes, and a long, deep skirt to provide maximum dielectric prote
Long Description	Buchanan, Wire Connector, WingTwist, Conductor Range: 22 - 10 AWG, 2/20 AWG Min, 3/10 Solid AWG MAX, Number Of Conductors: 1 to 6, Material: Flame-retardant Polypropelene, Color: Tan, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: WT41
Product Type	Wingtwist WT41 Tan, 500 Bag
Special Features	1,000V Maximum In Fixtures And Signs; Deep, Wide-Throated Skirt Protects Against Flash-Over And Turned-Back Strands For Maximum Dielectric Protection; Features: Five Color-Coded Models Cover Common Construction Wire Ranges; Fixed, Square-Wire Spring Threads Itself Creating Secure Pressure Grip; Green Model Designed For Ground Connections; Model Number: WT41; UL 486C Listed (WGR UL 467 Listed) And CSA C22.2 #188 Certified; Unique Contoured Wing Design Acts As Built-In Wrench Providing Maximum Torque With Minimum E
anufacturer Information	· · · · · · · · · · · · · · · · · · ·

Ma

Brand	Ideal	
GTIN	00781789967677	
Manufacturers Part Number	WT41-B	
UPC	781789967677	

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS

Availability

minimum qty	500

Packaging

······································		
Carton	500	
Weight Per each	0.004	

21330 Inverness Forest Blvd 77073-0000, TX Houston Phone: 832-626-1994 Fax: 832-626-1995

Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221
	<u>F)</u>
standard	CSA C22.2 #188, UL 486C Listed, RoHS