

# Eaton X67

Catalog Number: X67

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, X shape, 2"

Photo is representative

## General specifications

|   |                |
|---|----------------|
| Product Name  | Catalog Number |
| Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body | X67            |
|   | UPC            |
|   | 782274746807   |
| Product Length/Depth  | Product Height |
| 9.19 in   | 5.19 in        |
| Product Width   | Product Weight |
| 3.13 in   | 6.2 lb         |



## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

12

## Product specifications

### Shape

X

### Trade size

2"

### Material

Feraloy iron alloy

## Resources

### Catalogs

[Crouse-Hinds series Form 7 catalog page](#)

### Certification reports

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

### Installation instructions

[IF 863 - Conduit Body Wire Pulling](#)

[IF 964 - Conduit Body Wire Pulling](#)

### Specifications and datasheets

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

[Eaton Specification Sheet - X67](#)

### Technical service bulletins

[Industrial Fittings Wire Fill Chart](#)

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton X67

Catalog Number: X67

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, X shape, 2"

Photo is representative

## General specifications

|   |                       |
|---|-----------------------|
| <b>Product Name</b>   | <b>Catalog Number</b> |
| Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body | X67                   |
|   | <b>UPC</b>            |
|   | 782274746807          |
| <b>Product Length/Depth</b>                                   | <b>Product Height</b> |
| 9.19 in   | 5.19 in               |
| <b>Product Width</b>  | <b>Product Weight</b> |
| 3.13 in   | 6.2 lb                |



## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

12

## Product specifications

### Shape

X

### Trade size

2"

### Material

Feraloy iron alloy

## Resources

### Catalogs

[Crouse-Hinds series Form 7 catalog page](#)

### Certification reports

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

### Installation instructions

[IF 863 - Conduit Body Wire Pulling](#)

[IF 964 - Conduit Body Wire Pulling](#)

### Specifications and datasheets

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

[Eaton Specification Sheet - X67](#)

### Technical service bulletins

[Industrial Fittings Wire Fill Chart](#)

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)