



Powering Business Worldwide

pe.eaton.com



IDC Fuse Terminal Blocks

XBQT25FBE

UPC:782116926893

Dimensions:

- **Height:** X
- **Length:** 3.25 IN
- **Width:** .24 IN

Notes:As disconnect terminal block, 400V, as fuse terminal blocks 250V.

Warranties:

- 1 year

Specifications:

- **Type:** IEC-XB Series
- **Amperage Rating:** 15A (UL), 6.30A connection
- **Voltage Rating:** UL 300V
- **Maximum Wire Size:** 14 AWG/1.5 mm²
- **Quantity:** 50
- **Wire Size:** #20-14 AWG
- **Color:** Black

Supporting documents:

- [XB IEC TERMINAL BLOCKS](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XB IEC terminal blocks-versatility, quality, and reliability](#)
- [Eaton Specification Sheet - XBQT25FBE](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data



Powering Business Worldwide

pe.eaton.com



IDC Fuse Terminal Blocks

XBQT25FBE

UPC:782116926893

Dimensions:

- **Height:** X
- **Length:** 3.25 IN
- **Width:** .24 IN

Notes:As disconnect terminal block, 400V, as fuse terminal blocks 250V.

Warranties:

- 1 year

Specifications:

- **Type:** IEC-XB Series
- **Amperage Rating:** 15A (UL), 6.30A connection
- **Voltage Rating:** UL 300V
- **Maximum Wire Size:** 14 AWG/1.5 mm²
- **Quantity:** 50
- **Wire Size:** #20-14 AWG
- **Color:** Black

Supporting documents:

- [XB IEC TERMINAL BLOCKS](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XB IEC terminal blocks-versatility, quality, and reliability](#)
- [Eaton Specification Sheet - XBQT25FBE](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data