

Specifications



Eaton XBUT35

Eaton XB IEC terminal block, 16 mm Screw connection single level-through-feed, Gray, 8 AWG/6 mm² maximum wire, IEC 800V, EN 700V, UL 600V, IEC #24-8 AWG, EN #24-8 AWG, UL #24-8 AWG wire, IEC 57A, EN 40,50A, UL 50A

General specifications

PRODUCT NAME	Eaton XB IEC terminal block
CATALOG NUMBER	XBUT35
UPC	782116905065
PRODUCT LENGTH/DEPTH	2.37 in
PRODUCT HEIGHT	2.88 in
PRODUCT WIDTH	0.63 in
PRODUCT WEIGHT	0.02 lb
WARRANTY	1 year
CERTIFICATIONS	CSA Certified UL Listed

Product specifications

TYPE	IEC-XB Series
AMPERAGE RATING	527 (IEC), 40A (EN), 50A (EN), 50A (UL)
VOLTAGE RATING	IEC 800V, EN 700V, UL 600V

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - XBUT35
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Eaton XBUT35

Eaton XB IEC terminal block, 16 mm Screw connection single level-through-feed, Gray, 8 AWG/6 mm² maximum wire, IEC 800V, EN 700V, UL 600V, IEC #24-8 AWG, EN #24-8 AWG, UL #24-8 AWG wire, IEC 57A, EN 40,50A, UL 50A

General specifications

PRODUCT NAME	Eaton XB IEC terminal block
CATALOG NUMBER	XBUT35
UPC	782116905065
PRODUCT LENGTH/DEPTH	2.37 in
PRODUCT HEIGHT	2.88 in
PRODUCT WIDTH	0.63 in
PRODUCT WEIGHT	0.02 lb
WARRANTY	1 year
CERTIFICATIONS	CSA Certified UL Listed

Product specifications

TYPE	IEC-XB Series
AMPERAGE RATING	527 (IEC), 40A (EN), 50A (EN), 50A (UL)
VOLTAGE RATING	IEC 800V, EN 700V, UL 600V

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - XBUT35
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

