

Sali Insulating Bushings

Superior ADALET Laminated Insulation



FEATURES

- Sali bushings are machined from paper laminated phenolic material and comply with NEMA-X phenolic material specifications.
- 11,000 psi tensile
- 17,000 flexural
- 450v/mil dielectric
- Heat resistance - 150° C, continuous
- Moisture absorption - 1/2 of 1%
- Listed by Underwriters Laboratories for your quality assurance.
- Sali bushings have been repeatedly proved in a wide variety of applications over a 25 year period.

TYPE PE-FEMALE-DEEP-THREADED

Catalog #	Conduit Size (in.)	Nominal Dimensions (in.)			Std. Package	
		I.D.	O.D.	Height	Qty.	Weight (lbs. per 100)
PE-2	½	⅝	1 ⅛	⅝	50	1 ½
PE-3	¾	1⅜	1 ⅝	⅝	50	2
PE-4	1	1	1 ⅝	2⅝/32	50	3 ½
PE-5	1 ¼	1 ⅝	2	2⅝/32	25	4 ½
PE-6	1 ½	1 ⅝	2 ¼	2⅝/32	25	5 ½
PE-8	2	2	2 ¾	2⅝/32	10	7 ½
PE-10	2 ½	2 ⅞	3 ¼	1	5	12
PE-12	3	3	3 ⅞	1 ⅞	5	16
PE-14	3 ½	3 ½	4 ⅜	1 ⅞	5	19
PE-16	4	4	5	1 ⅞	2	24

Recommended for rigid conduit or in combination with male type PEM bushing when maximum thread engagement is required.

Certifications

UL Listed E10016



Sali Insulating Bushings

Superior ADALET Laminated Insulation



FEATURES

- Sali bushings are machined from paper laminated phenolic material and comply with NEMA-X phenolic material specifications.
- 11,000 psi tensile
- 17,000 flexural
- 450v/mil dielectric
- Heat resistance - 150° C, continuous
- Moisture absorption - 1/2 of 1%
- Listed by Underwriters Laboratories for your quality assurance.
- Sali bushings have been repeatedly proved in a wide variety of applications over a 25 year period.

TYPE PE-FEMALE-DEEP-THREADED

Catalog #	Conduit Size (in.)	Nominal Dimensions (in.)			Std. Package	
		I.D.	O.D.	Height	Qty.	Weight (lbs. per 100)
PE-2	½	⅝	1 ⅛	⅝	50	1 ½
PE-3	¾	1⅜	1 ⅝	⅝	50	2
PE-4	1	1	1 ⅝	2⅝	50	3 ½
PE-5	1 ¼	1 ⅝	2	2⅝	25	4 ½
PE-6	1 ½	1 ⅝	2 ¼	2⅝	25	5 ½
PE-8	2	2	2 ¾	2⅝	10	7 ½
PE-10	2 ½	2 ⅞	3 ¼	1	5	12
PE-12	3	3	3 ⅞	1 ⅞	5	16
PE-14	3 ½	3 ½	4 ⅜	1 ⅞	5	19
PE-16	4	4	5	1 ⅞	2	24

Recommended for rigid conduit or in combination with male type PEM bushing when maximum thread engagement is required.

Certifications

UL Listed E10016

