

# Specifications

Photo is representative

## Eaton XJG24 HDG

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Steel, Hot dip galvanized finish, 4" maximum conduit movement, 3/4" trade size

### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary, Hazardous Locations
----------------------------	-------------------------------

<b>STANDARDS TYPE</b>	NEC/CEC
-----------------------	---------

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series XJG expansion coupling
<b>CATALOG NUMBER</b>	XJG24 HDG
<b>UPC</b>	662276290167
<b>PRODUCT LENGTH/DEPTH</b>	7 in
<b>PRODUCT HEIGHT</b>	2.25 in
<b>PRODUCT WIDTH</b>	2.25 in
<b>PRODUCT WEIGHT</b>	2.15 lb



Powering Business Worldwide

# Specifications

Photo is representative

## Eaton XJG24 HDG

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Steel, Hot dip galvanized finish, 4" maximum conduit movement, 3/4" trade size

### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary, Hazardous Locations
----------------------------	-------------------------------

<b>STANDARDS TYPE</b>	NEC/CEC
-----------------------	---------

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series XJG expansion coupling
<b>CATALOG NUMBER</b>	XJG24 HDG
<b>UPC</b>	662276290167
<b>PRODUCT LENGTH/DEPTH</b>	7 in
<b>PRODUCT HEIGHT</b>	2.25 in
<b>PRODUCT WIDTH</b>	2.25 in
<b>PRODUCT WEIGHT</b>	2.15 lb



Powering Business Worldwide