

Specifications

Eaton XJG34 SA



Photo is representative

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Copper-free aluminum, 4" maximum conduit movement, 1" trade size

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series XJG expansion coupling
CATALOG NUMBER	XJG34 SA
UPC	782274915807
PRODUCT LENGTH/DEPTH	7.38 in
PRODUCT HEIGHT	2.43 in
PRODUCT WIDTH	2.43 in
PRODUCT WEIGHT	1.2 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Resources

BROCHURES	Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure
CATALOGS	Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page
CERTIFICATION REPORTS	XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification
INSTALLATION INSTRUCTIONS	IF 343 - Type XJ Expansion Joints IF 1508 - Assembly-Free XJG
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - XJG34 SA Expansion and Deflection Couplings

Product specifications

TYPE	Expansion
CONDUIT TYPE	Rigid/IMC
TRADE SIZE	1"
CONDUIT MOVEMENT - MAX	4"
MATERIAL	Copper-free aluminum

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.