

# Specifications

## Eaton XJG54 SA



Photo is representative

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Copper-free aluminum, 4" maximum conduit movement, 1-1/2" trade size

### General specifications

|                      |                                                  |
|----------------------|--------------------------------------------------|
| PRODUCT NAME         | Eaton Crouse-Hinds series XJG expansion coupling |
| CATALOG NUMBER       | XJG54 SA                                         |
| UPC                  | 782274915883                                     |
| PRODUCT LENGTH/DEPTH | 8 in                                             |
| PRODUCT HEIGHT       | 3.62 in                                          |
| PRODUCT WIDTH        | 3.62 in                                          |
| PRODUCT WEIGHT       | 2.55 lb                                          |

## Certifications and compliances

|                     |                                  |
|---------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE      | NEC/CEC                          |

## Resources

|                               |                                                                                                                                                                                        |
|-------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| BROCHURES                     | <a href="#">Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure</a>                                                                                                    |
| CATALOGS                      | <a href="#">Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page</a>                                                                                         |
| CERTIFICATION REPORTS         | <a href="#">XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification</a><br><a href="#">XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification</a> |
| INSTALLATION INSTRUCTIONS     | <a href="#">IF 343 - Type XJ Expansion Joints</a><br><a href="#">IF 1508 - Assembly-Free XJG</a>                                                                                       |
| SPECIFICATIONS AND DATASHEETS | <a href="#">Expansion and Deflection Couplings</a><br><a href="#">Eaton Specification Sheet - XJG54 SA</a>                                                                             |

## Product specifications

|                        |                      |
|------------------------|----------------------|
| TYPE                   | Expansion            |
| CONDUIT TYPE           | Rigid/IMC            |
| TRADE SIZE             | 1-1/2"               |
| CONDUIT MOVEMENT - MAX | 4"                   |
| MATERIAL               | Copper-free aluminum |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.