

Specifications

Eaton XJG64 HDG

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Steel, Hot dip galvanized finish, 4" maximum conduit movement, 2" trade size



Photo is representative

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series XJG expansion coupling
CATALOG NUMBER	XJG64 HDG
UPC	662276271517
PRODUCT LENGTH/DEPTH	8.75 in
PRODUCT HEIGHT	4.38 in
PRODUCT WIDTH	4.38 in
PRODUCT WEIGHT	8.9 lb



Certifications and compliances

AREA CLASSIFICATION Ordinary/Non-Hazardous

Product specifications

TYPE Expansion

	Locations
STANDARDS TYPE	NEC/CEC

CONDUIT TYPE	Rigid/IMC
TRADE SIZE	2"
CONDUIT MOVEMENT - MAX	4"
MATERIAL	Steel
FINISH	Hot dip galvanized

Resources

BROCHURES	Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure Crouse-Hinds series Hot Dip Galvanized Products brochure
CATALOGS	Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page
CERTIFICATION REPORTS	XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification
INSTALLATION INSTRUCTIONS	IF 1508 - Assembly-Free XJG IF 343 - Type XJ Expansion Joints
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - XJG64 HDG Expansion and Deflection Couplings

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications

Eaton XJG64 HDG

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Steel, Hot dip galvanized finish, 4" maximum conduit movement, 2" trade size



Photo is representative

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series XJG expansion coupling
CATALOG NUMBER	XJG64 HDG
UPC	662276271517
PRODUCT LENGTH/DEPTH	8.75 in
PRODUCT HEIGHT	4.38 in
PRODUCT WIDTH	4.38 in
PRODUCT WEIGHT	8.9 lb



Certifications and compliances

AREA CLASSIFICATION Ordinary/Non-Hazardous

Product specifications

TYPE Expansion

	Locations
STANDARDS TYPE	NEC/CEC

CONDUIT TYPE	Rigid/IMC
TRADE SIZE	2"
CONDUIT MOVEMENT - MAX	4"
MATERIAL	Steel
FINISH	Hot dip galvanized

Resources

BROCHURES	Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure Crouse-Hinds series Hot Dip Galvanized Products brochure
CATALOGS	Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page
CERTIFICATION REPORTS	XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification
INSTALLATION INSTRUCTIONS	IF 1508 - Assembly-Free XJG IF 343 - Type XJ Expansion Joints
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - XJG64 HDG Expansion and Deflection Couplings

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

