

Specifications

Photo is representative

Eaton XJG64 HDG

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Steel, Hot dip galvanized finish, 4" maximum conduit movement, 2" trade size

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series XJG expansion coupling
CATALOG NUMBER	XJG64 HDG
UPC	662276271517
PRODUCT LENGTH/DEPTH	8.75 in
PRODUCT HEIGHT	4.38 in
PRODUCT WIDTH	4.38 in
PRODUCT WEIGHT	8.9 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

TYPE	Expansion
CONDUIT TYPE	Rigid/IMC
TRADE SIZE	2"
CONDUIT MOVEMENT - MAX	4"
MATERIAL	Steel
FINISH	Hot dip galvanized

Resources

BROCHURES [Crouse-Hinds series Hot Dip Galvanized Products brochure](#)

[Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure](#)

CATALOGS [Crouse-Hinds series XIG Conduit Expansion Couplings for Rigid/IMC catalog page](#)

CERTIFICATION REPORTS [XIG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification](#)

[XIG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification](#)

INSTALLATION INSTRUCTIONS [IF 343 - Type XJ Expansion Joints](#)
[IF 1508 - Assembly-Free XIG](#)

SPECIFICATIONS AND DATASHEETS [Expansion and Deflection Couplings](#)
[Eaton Specification Sheet - XIG64 HDG](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

