

Specifications

Photo is representative

Eaton XJG68 SA

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Copper-free aluminum, 8" maximum conduit movement, 2" trade size

Certifications and compliances

AREA CLASSIFICATION	Ordinary, Hazardous Location
----------------------------	------------------------------

STANDARDS TYPE	NEC/CEC
-----------------------	---------

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series XJG expansion coupling
CATALOG NUMBER	XJG68 SA
UPC	782274915937
PRODUCT LENGTH/DEPTH	12.75 in
PRODUCT HEIGHT	4.38 in
PRODUCT WIDTH	4.38 in
PRODUCT WEIGHT	4.7 lb



Powering Business Worldwide

Specifications

Photo is representative

Eaton XJG68 SA

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Copper-free aluminum, 8" maximum conduit movement, 2" trade size

Certifications and compliances

AREA CLASSIFICATION	Ordinary, Hazardous Locations
----------------------------	-------------------------------

STANDARDS TYPE	NEC/CEC
-----------------------	---------

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series XJG expansion coupling
CATALOG NUMBER	XJG68 SA
UPC	782274915937
PRODUCT LENGTH/DEPTH	12.75 in
PRODUCT HEIGHT	4.38 in
PRODUCT WIDTH	4.38 in
PRODUCT WEIGHT	4.7 lb



Powering Business Worldwide