

Specifications

Photo is representative

Eaton XTCE032C01C

Eaton XT IEC contactor, 32A, 412 Vac 50 Hz, 480 Vac 60 Hz, 1NC, 32A, Frame C, 45 mm, 50-60 Hz, 3, 5, 5/ 10, 10, 20, 25 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor

General specifications

PRODUCT NAME	Eaton XT IEC contactor
CATALOG NUMBER	XTCE032C01C
UPC	782116485925
PRODUCT LENGTH/DEPTH	3.425 in
PRODUCT HEIGHT	3.898 in
PRODUCT WIDTH	1.85 in
PRODUCT WEIGHT	0.9 lb
WARRANTY	1 year
COMPLIANCES	RoHS Compliant CE Marked
CERTIFICATIONS	UL Listed CSA Certified EN 60947 IEC 60947
CATALOG NOTES	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

Product specifications

AMPERAGE RATING	32A
HP RATING - MAX	3, 5, 5/ 10, 10, 20, 25 hp (1/3PH @115,200,230/200,230,460,575 V)
NUMBER OF POLES	Three-pole
TYPE	Full voltage non-reversing contactor
FREQUENCY RATING	50-60 Hz
FRAME SIZE	45 mm
TERMINALS	Screw terminals
COIL VOLTAGE	412-480 Vac, 50/60 Hz
CONTACT CONFIGURATION	1 NC
CONTINUOUS AMPERE RATING	32 A
SERIES	XT IEC
OPERATION	Non-reversing

Resources

CATALOGS

[Motor Control and Protection, IEC Contactors and Starters, Volume 5, Tab 1](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - XTCE032C01C](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Photo is representative

Eaton XTCE032C01C

Eaton XT IEC contactor, 32A, 412 Vac 50 Hz, 480 Vac 60 Hz, 1NC, 32A, Frame C, 45 mm, 50-60 Hz, 3, 5, 5/ 10, 10, 20, 25 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor

General specifications

PRODUCT NAME	Eaton XT IEC contactor
CATALOG NUMBER	XTCE032C01C
UPC	782116485925
PRODUCT LENGTH/DEPTH	3.425 in
PRODUCT HEIGHT	3.898 in
PRODUCT WIDTH	1.85 in
PRODUCT WEIGHT	0.9 lb
WARRANTY	1 year
COMPLIANCES	RoHS Compliant CE Marked
CERTIFICATIONS	UL Listed CSA Certified EN 60947 IEC 60947
CATALOG NOTES	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

Product specifications

AMPERAGE RATING	32A
HP RATING - MAX	3, 5, 5/ 10, 10, 20, 25 hp (1/3PH @115,200,230/200,230,460,575 V)
NUMBER OF POLES	Three-pole
TYPE	Full voltage non-reversing contactor
FREQUENCY RATING	50-60 Hz
FRAME SIZE	45 mm
TERMINALS	Screw terminals
COIL VOLTAGE	412-480 Vac, 50/60 Hz
CONTACT CONFIGURATION	1 NC
CONTINUOUS AMPERE RATING	32 A
SERIES	XT IEC
OPERATION	Non-reversing

Resources

CATALOGS

[Motor Control and Protection, IEC Contactors and Starters, Volume 5, Tab 1](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - XTCE032C01C](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

