

# Specifications

Photo is representative



## Eaton XTCE115GS1A

Eaton XT IEC contactor, 115A, Side-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, Frame G, 90 mm, 50-60 Hz, 10, 25, 25/40, 50, 100, 100 hp (1/3PH @ 115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR

### General specifications

<b>PRODUCT NAME</b>	Eaton XT IEC contactor
<b>CATALOG NUMBER</b>	XTCE115GS1A
<b>UPC</b>	786685365152
<b>PRODUCT LENGTH/DEPTH</b>	1 in
<b>PRODUCT HEIGHT</b>	1 in
<b>PRODUCT WIDTH</b>	1 in
<b>PRODUCT WEIGHT</b>	1 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	CSA Certified UL Listed EN 60947 IEC 60947

### Product specification

<b>AMPERAGE RATING</b>	115A
<b>HP RATING - MAX</b>	10, 25 (1/3PH @ 115 V)
<b>NUMBER OF POLES</b>	Three
<b>TYPE</b>	Full voltage contactor
<b>FREQUENCY RATING</b>	50-60
<b>FRAME SIZE</b>	90 mm
<b>TERMINALS</b>	Screw
<b>COIL</b>	110-1
<b>COIL VOLTAGE</b>	110-1
<b>CONTACT CONFIGURATION</b>	1 NO
<b>CONTINUOUS AMPERE RATING</b>	115 A
<b>SERIES</b>	XT IE
<b>OPERATION</b>	Non-r

# Specifications

Photo is representative



## Eaton XTCE115GS1A

Eaton XT IEC contactor, 115A, Side-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, Frame G, 90 mm, 50-60 Hz, 10, 25, 25/40, 50, 100, 100 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR

### General specifications

<b>PRODUCT NAME</b>	Eaton XT IEC contactor
<b>CATALOG NUMBER</b>	XTCE115GS1A
<b>UPC</b>	786685365152
<b>PRODUCT LENGTH/DEPTH</b>	1 in
<b>PRODUCT HEIGHT</b>	1 in
<b>PRODUCT WIDTH</b>	1 in
<b>PRODUCT WEIGHT</b>	1 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	CSA Certified UL Listed EN 60947 IEC 60947

### Product specification

<b>AMPERAGE RATING</b>	115A
<b>HP RATING - MAX</b>	10, 25 (1/3PH @115 V)
<b>NUMBER OF POLES</b>	Three
<b>TYPE</b>	Full voltage contactor
<b>FREQUENCY RATING</b>	50-60
<b>FRAME SIZE</b>	90 mm
<b>TERMINALS</b>	Screw
<b>COIL</b>	110-1
<b>COIL VOLTAGE</b>	110-1
<b>CONTACT CONFIGURATION</b>	1 NO
<b>CONTINUOUS AMPERE RATING</b>	115 A
<b>SERIES</b>	XT IE
<b>OPERATION</b>	Non-r