

Specifications

Photo is representative

Eaton XTCE115GS1A

Eaton XT IEC contactor, 115A, Side-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, Frame G, 90 mm, 50-60 Hz, 10, 25, 25/40, 50, 100, 100 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR

Product specification

AMPERAGE RATING	115A
HP RATING - MAX	10, 25 (1/3PH @115 V)
NUMBER OF POLES	Three
TYPE	Full v contactor
FREQUENCY RATING	50-60
FRAME SIZE	90 mm
TERMINALS	Screw
COIL	110-1
COIL VOLTAGE	110-1
CONTACT CONFIGURATION	1 NO
CONTINUOUS AMPERE RATING	115 A
SERIES	XT IE
OPERATION	Non-r

General specifications

PRODUCT NAME	Eaton XT IEC contactor
CATALOG NUMBER	XTCE115GS1A
UPC	786685365152
PRODUCT LENGTH/DEPTH	1 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	1 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	CSA Certified UL Listed EN 60947 IEC 60947



Powering Business Worldwide