

# Specifications



## Eaton XTCR080F11A

Eaton XT IEC contactor, 80A, Top-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 80A, Frame F, 90 mm, 50-60 Hz, 7.5, 15/ 25, 30, 60, 75 hp (1/3PH @115, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVR

### General specifications

<b>PRODUCT NAME</b>	Eaton XT IEC contactor
<b>CATALOG NUMBER</b>	XTCR080F11A
<b>UPC</b>	782116356126
<b>PRODUCT LENGTH/DEPTH</b>	9.5 in
<b>PRODUCT HEIGHT</b>	6 in
<b>PRODUCT WIDTH</b>	6.5 in
<b>PRODUCT WEIGHT</b>	4.7 lb
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	UL Listed CSA Certified IEC 60947 EN 60947
<b>CATALOG NOTES</b>	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## Product specifications

AMPERAGE RATING	80A
HP RATING - MAX	7.5, 15/ 25, 30, 60, 75 hp (1/3PH @115,230/200,230,460,575 V)
NUMBER OF POLES	Three-pole
TYPE	Full voltage reversing contactor
FREQUENCY RATING	50-60 Hz
TERMINALS	Screw terminals
COIL VOLTAGE	110-120 Vac, 50/60 Hz
CONTACT CONFIGURATION	1 NO, 1 NC
CONTINUOUS AMPERE RATING	80 A
SERIES	XT IEC
OPERATION	Reversing

## Resources

### CATALOGS

[Motor Control and  
Protection, IEC Contactors  
and Starters, Volume 5,  
Tab 1](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet -  
XTCR080F11A](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton XTCR080F11A

Eaton XT IEC contactor, 80A, Top-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 80A, Frame F, 90 mm, 50-60 Hz, 7.5, 15/ 25, 30, 60, 75 hp (1/3PH @115, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVR

### General specifications

<b>PRODUCT NAME</b>	Eaton XT IEC contactor
<b>CATALOG NUMBER</b>	XTCR080F11A
<b>UPC</b>	782116356126
<b>PRODUCT LENGTH/DEPTH</b>	9.5 in
<b>PRODUCT HEIGHT</b>	6 in
<b>PRODUCT WIDTH</b>	6.5 in
<b>PRODUCT WEIGHT</b>	4.7 lb
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	UL Listed CSA Certified IEC 60947 EN 60947
<b>CATALOG NOTES</b>	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## Product specifications

AMPERAGE RATING	80A
HP RATING - MAX	7.5, 15/ 25, 30, 60, 75 hp (1/3PH @115,230/200,230,460,575 V)
NUMBER OF POLES	Three-pole
TYPE	Full voltage reversing contactor
FREQUENCY RATING	50-60 Hz
TERMINALS	Screw terminals
COIL VOLTAGE	110-120 Vac, 50/60 Hz
CONTACT CONFIGURATION	1 NO, 1 NC
CONTINUOUS AMPERE RATING	80 A
SERIES	XT IEC
OPERATION	Reversing

## Resources

### CATALOGS

[Motor Control and  
Protection, IEC Contactors  
and Starters, Volume 5,  
Tab 1](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet -  
XTCR080F11A](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

