



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YA34L2NTCFX YA34L-2NTCFX

Burndy LLC

Catalog Number	YA34L2NTCFX
Manufacturer	Burndy LLC
Description	350 Kcmil G, H, I, K, M, 373 Dlo Cu, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/Csa, 90 C, Up to 35KV, Blue Color Code, 19 Die Index.
Weight per unit	0.5200 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	19
Material	Copper
pallet quantity	2880
Voltage Rating	35

Material, Color, and Finish

Color Code	BLUE
------------	------

Descriptions

Description	YA34L-2NTCFX
extra long description	BUR YA34L2NTCFX HYLUG-350 FLEX-NEMA
Long Description	350 kcmil G,H,I,K,M,373 DLO CU, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, Blue Color Code, 19 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Finish: Electro-Tin Plated, Tongue Angle: Straight, Wire Strip Length: 1-1/4 IN, Temperature Rating: 90 DEG C, Die Index: 19, Color Code: Blue, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W32VT Die, (2), Hydraulic: BCT500HS, Y500CTHS Tool, W32VT, W32RT Die, (2), Y35, Y39, Y750, PAT750 Tool, U32RT Die, (2), Y46 Tool, U32RT Die With PUADP-1 Adapter, (2), Conductor Type: Flexi



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	BURNDY
GTIN	00781810018484
Manufacturers Part Number	YA34L2NTCFX
UPC	781810018484

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel, Tin Plated

Packaging

Carton	1
Package	40
Weight Per each	0.52

Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B