



BURNDY Catalog Number
UPC Number
Description
Status

YA6CTC38
7818105659955
CU HYLUG, 6AWG,3/8 STUD
Active

Web Use
BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Length (in)	2.21
Barrell Style	Skived
Barrel Type	Long
Thickness	0.06
B Length (in)	1.12
Pad Width (in)	0.58
Strip Length	1-3/16
General	
Product Description	Uninsulated CU Compression Terminal, One Hole Long Barrel with No Inspection window, Stud Hole Size: 3/8 IN, Conductor: #6 AWG
Conductor(s)	
Copper Solid Size (Range)	6 AWG
Navy Cable Size (Range)	N/A
Copper Stranded (Range)	6 AWG
Physical	
Type of Plating	Tin
Color Code	Blue
Plated (Yes or No)	Y
Index Number	7,374
Product Material	Copper
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175