



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YA8CTC38  
 7818100204188  
 CUHYLUG-8 STR-1 HOLE-3/8  
 Active

**Web Use**  
 BURNDY Product Line

**Dimensional**

Tongue Angle	Straight
Length (in)	1.88
Barrell Style	Chamfered
Bolt Hole Size (in)	0.39
Barrel Type	Long
Thickness	0.06
B Length (in)	0.81
Pad Width (in)	0.58
Strip Length	1-3/16

**General**

Number of Holes	1
Product Description	Copper Compression Lug, 1 Hole w/o Inspection Window, #8 AWG, 3/8" Stud, Long Barrel, Tin Plated

**Conductor(s)**

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	6 AWG
DLO Size (Range)	N/A
Copper Stranded (Range)	8 AWG

**Physical**

Type of Plating	Tin - Electro Plated
Bolt Hole Size	3/8
Color Code	Red
Plated (Yes or No)	Y
Index Number	49
Product Material	Copper

**Approvals / Certifications**

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL467

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175