



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YS6CLBOX #6 STR Cu Butt Splice

Burndy LLC

Catalog Number	YS6CLBOX
Manufacturer	Burndy LLC
Description	6 Awg Cu, Standard Barrel, Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Blue Color Code, 7 or 374 Die Index
Weight per unit	0.0200 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	7
Material	Copper
Voltage Rating	35

Material, Color, and Finish

Color Code	BLUE
Finish	Tin-Plated

Descriptions

Description	#6 STR CU BUTT SPLICE
extra long description	BUR YS6CLBOX 6 STR. CU. BUTT SPLICE
Long Description	6 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, BLUE Color Code, 7 or 374 Die Index
Product Type	Splice
Special Features	Features: Standard Barrel Length, Ideal For Limited Space Applications While Providing Ample Barrel Length For Proper Crimp, Four (4) Center Conductor Stops, Provides A Center Wire Stop For Proper Conductor Insertion, Conductor Type: Commercial Stranded Copper, Die Index: 7 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: Y1MRTC, Y2MR Tool, (1), MD7-34R Tool, W5CVT Die, (1), MD6, OUR840 Tool, X5CRT Die, (1), Y35, Y39, Y750, Y46 Tool, U5CRT Die, (1), Color Code: Blue, Dieless To

Manufacturer Information

Brand	BURNDY
GTIN	00781810555750
Manufacturers Part Number	YS6CLBOX
UPC	781810555750

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	YS-L, Standard Barrel



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	50
Weight Per each	0.02

Uses, Certifications, and Standards

Application	Wire Splice
standard	UL 486A-486B