



YSHG4429

by Burndy
Catalog ID: YSHG4429

Prop 65 Notice

Copper Compression Double H- Tap Connector, 2 AWG - 250 kcmil (Tap), #8 & #9 Rebar/ 1" Ground Rod.

Features: UL467 Listed: Suitable For Direct Burial In Earth Or Concrete, Material Is High Conductivity Copper Extrusion: Minimizes Resistance, Eliminates Corrosion Due To Dissimilar Metals, Grooves Are Prefilled With PENETROX E2 Oxide Inhibitor And Individually Sealed: Inhibits Moisture And Contaminants Ensuring Electrical Integrity, Ground Rod Size: 1 IN, Tools, Die Set Catalog Number, And (number Of Crimps): Y46 Tool, PYFR Die, (2), Rebar Size: #8, #9, Wire Entry: Double, Conductor Type: Run: Rebar, Ground Rod, Tap1: Copper Wire, Tap2: Copper Wire, Tap3: Copper Wire, Die Index: KR Element A, Shape: H, Conductor Size (tap Range): 2 AWG - 250 KCMIL

Product Details

General

Application	For Direct Burial In Earth Or Concrete
Connector Type	H-Tap
Die Index	KR
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	HYGROUND®
Type	Taps
UPC	781810128657
UPC 12 Digit	7818101286577

Dimensions

Dimension - Length Overall inch	2.44 in
Dimension - Width inch	3.22 in
Dimension - Width mm	82 mm

Conductor Related

Conductor - Copper Str Tap	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Tap Range	2 AWG-250 kcmil
Conductor - Rebar Run	8 ;9
Conductor - Rebar Run Range	8 -9
Conductor - Rod Run	1 in
Conductor - Rod Run Range	1 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 467, Direct Burial
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)