

Specifications



Photo is representative

Eaton AHAC-P-1500-DMV

Eaton ceiling sensor, Dual relay, 120 to 347 VAC, Maintained closure, White, 32 kHz, Incand, MLV, halo, 1500 sq ft, Occupancy 748820

General specifications

PRODUCT NAME	Eaton ceiling sensor
CATALOG NUMBER	AHAC-P-1500-DMV
UPC	032664748820
PRODUCT LENGTH/DEPTH	4.5 in
PRODUCT HEIGHT	1.42 in
PRODUCT WIDTH	0.8 in
PRODUCT WEIGHT	1 lb
CERTIFICATIONS	NOM cULus Listed
PRODUCT TYPE	Ceiling sensor



Powering Business Worldwide

Product specifications

FREQUENCY RATING	32 kHz
SPECIAL FEATURES	Dual relay
TYPE	Ceiling sensor
VOLTAGE RATING	120 to 347 Vac
SENSOR TYPE	Occupancy
CLOSURE TYPE	Maintained
LOAD TYPE	INC MLV HAL
RANGE	1500 sq ft
COLOR	White

Resources

BROCHURES	Commercial ceiling sensors sell sheet Arrow Hart commercial lighting controls brochure
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - AHAC-P-1500-DMV

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

