



GE
Lighting

95927 - GE LED A19 60w Replacement

LED11DAV3/5k

GENERAL CHARACTERISTICS

Lamp Type	A19
Product Color	White
Product Technology	LED
Rated Life (Hours)	15000 h
Bulb Shape	A19

PHOTOMETRIC CHARACTERISTICS

Center Beam Candle Pwr Candela	0 cd
Nominal Initial Lumen per Watt	87
Initial Lumens-nominal	850 lm
Color Rendering Index-CRI	80
Color Temperature	5000 K

PRODUCT INFORMATION

Product Code	95927
Description	LED11DAV3/5k
Alternative Unit Of Measure	CASE

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Rated power (Watts)	11 W



GE
Lighting

95927 - GE LED A19 60w Replacement

LED11DAV3/5k

GENERAL CHARACTERISTICS

Lamp Type	A19
Product Color	White
Product Technology	LED
Rated Life (Hours)	15000 h
Bulb Shape	A19

PHOTOMETRIC CHARACTERISTICS

Center Beam Candle Pwr Candela	0 cd
Nominal Initial Lumen per Watt	87
Initial Lumens-nominal	850 lm
Color Rendering Index-CRI	80
Color Temperature	5000 K

PRODUCT INFORMATION

Product Code	95927
Description	LED11DAV3/5k
Alternative Unit Of Measure	CASE

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Rated power (Watts)	11 W