



Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500311-009

Atwell

Atwell Collection 1-Light Clear Glass Globe Brushed Nickel Modern Large Pendant Hanging Light

Category: Pendants
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Round



Length: 12 in
Diameter: 12 in
Height: 12-1/2 in
Overall Ht. W/Cord: 132-1/2 in

Clear Glass Round
Width: 12 in
Height: 12 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Cord	10 feet of wire supplied	Quantity: one 60 W max.	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 V	E26 base Porcelain Socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.5" W., 5.5" ht., 1.062" depth			



Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500311-009

Atwell

Atwell Collection 1-Light Clear Glass Globe Brushed Nickel Modern Large Pendant Hanging Light

Category: Pendants
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Round



Length: 12 in
Diameter: 12 in
Height: 12-1/2 in
Overall Ht. W/Cord: 132-1/2 in

Clear Glass Round
Width: 12 in
Height: 12 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Cord	10 feet of wire supplied	Quantity: one 60 W max.	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 V	E26 base Porcelain Socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.5" W., 5.5" ht., 1.062" depth			